



Pass and Seymour
Medium-Duty, Short Length, Flexible Eye, T-Type
Part No. PM1001



Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 1.000-1.490-inch, Mesh Length - 24-inch, Eye Diameter - 5/16-inch, Break Strength - 9,600 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 24: Eye Diameter: 5/16

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	1 in	Minimum Cable Range	1.49 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 9600		