

Medium duty, Flexible eye. Cable diameter - 1.500-1.740", Mesh Length - 36", Break Strength - 8,100 lbs.



## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

## Specifications

### General Info

UPC Number	785007993585	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

### Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 1.500-1.740: Mesh Length: 36
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 8,100