



Pass and Seymour
Medium Duty, Short Length, Flexible Eye, T-Type
Part No. PM1501

Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 1.500-1.990", Mesh Length - 24", Eye Diameter - 7/16", Break Strength - 16,400 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007185218 |
| Country Of Origin | Mexico | Construction | Various Types of Pulling, Support and Strain Relief Grips |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Technical Information

| | | | |
|----------|--|------------|--|
| Capacity | Various Cable Diameter Ranges | Cable Size | Cable Dia. Range: 1.500-1.990: Mesh Length: 24: Eye Diameter: 7/16 |
| Mounting | Consult the Factory for Mounting Recommendations | Load | Approx. Break Strength: 16,400 |