Pass and Seymour

Medium Duty, Standard Length, Flexible Eye, T-Type

Part No. PM2502

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 2.500-2.990-inch, Mesh Length - 36-inch, Eye Diameter - 1/2-inch, Break Strength - 24,500 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Mesh Length: 36: Eye Diameter: 1/2

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	2.5 in	Minimum Cable Range	2.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 24500		