



Pass and Seymour
Medium-Duty, Long Length, Flexible Eye
Part No. PM2503

Medium-Duty, Long Length, Flexible Eye. Cable Diameter - 2.500-2.990-inch, Mesh Length - 48-inch, Break Strength - 25,900 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 48

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185287
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	2.5 in	Minimum Cable Range	2.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations