



Pass and Seymour
Medium Duty, Short Length, Flexible Eye, T-Type
Part No. PM3501



Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 3.500-3.990-inch, Mesh Length - 26-inch, Eye Diameter - 5/8-inch, Break Strength - 31,000 lbs.

Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 26: Eye Diameter: 5/8

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185409
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	3.5 in	Minimum Cable Range	3.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations