



**Pass and Seymour**  
**Medium Duty, Standard Length, Flexible Eye, T-Type**  
Part No. PM3502

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 3.500-3.990", Mesh Length - 40", Eye Diameter - 5/8", 31,000 lbs.



## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

## Specifications

### General Info

UPC Number	785007185331	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

### Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 3.500-3.990: Mesh Length: 40: Eye Diameter: 5/8
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 31,000