



Infinium 384 Offers ultra-high density Mini Duplex Connector (MDC) pass-through adapters which are organized to maximize fiber density while using the flexible and robust MDC connectors. These 1RU panels offer a density of 384 fibers (192 MDC Connectors) in a single unit of rack space. These panels have a front door to provide a clean look and to help protect the delicate cables. The rear support plate comes with two Multi-Use Mounting plates that feature eight HiLOC cradles. For cable management both the front and rear of the panel have several tiedown points to ensure proper routing, protection and a clean look for the fiber cables housed within the panel. The construction of the panel is powder-coated steel and is designed for optimal performance.

## Features & Benefits

### Panel Door

These panels have a front door to provide a clean look and to help protect the delicate cables

### Cable Management Front

Four individual tie downs provide proper routing and protection of cables. While the front pillars ensure that cables do not pass the side egress point

### Cable Management Rear

The rear support plate come with two Multi-Use Mounting plates that feature eight HiLOC cradles for quick and easy secure trunk mounting. While the rear support plate has 22 tie down points and 4 rear lip tie downs to maximize cable management and ensure proper routing

### Splicing:

The rear support plate also offers compatibility with the FST3-A144 splice tray, enabling ribbon splicing on this panel.

Includes Infinium 1U MDC Rack Mount Adapter Panel, Hook & Loop Straps, HiLoc Cradles, Mounting Hardware

## Specifications

### General Info

Product Line	Ortronics	Color	Magnesium
Country Of Origin	Mexico	Type	Patch Panel

### Technical Information

Rack Units	1U	Number of Ports	384
Mounting	Rack Mount		