



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/6' cord/Value Grade Surge
Part No. PR610N



Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Features & Benefits

Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776130072
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	11.73 in	Product Height US	1.5 in
Product Length US	2.24 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Connection	Cord-ended	Class	75
------------	------------	-------	----

Amperage	15 A	Short Circuit Rating	6500A
Type of Indicators	Light	Voltage	120.0 V