

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 0.750-0.990-inch, Mesh Length - 32-inch, Eye Diameter - 1-inch, Break Strength - 9,600 lbs.



## Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007994377
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 0.750-0.990: Mesh Length: 32: Eye Diameter: 1
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 9,600