



1pole Toggle Switch, Back & Side Wire, 15amp 120/277volt, Gray

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Brown

UPC Number 785007196504

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Standard UL 20

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

Technical Information

Wattage	1 W
----------------	-----

Number of Poles	Single Pole
------------------------	-------------

Voltage	120 V
----------------	-------

Closed Contact Resistance	Toggle
----------------------------------	--------

Contact Rating	15amp, 120/277vac
-----------------------	-------------------
