



Legrand

Industrial Extra Heavy-Duty Specification Grade Lock Switch, Back & Side Wire, Gray

Part No. PS15AC1L



1pole Lock Switch, Back & Side Wire, 15amp 120/277volt, Gray (Key can be removed in both positions)

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Gray

UPC Number 785007195590

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Standard UL20

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

Technical Information

Number of Poles	Single Pole
------------------------	-------------

Voltage	120 V
----------------	-------

Actuator	Toggle
-----------------	--------

Contact Rating	15Amp, 120/277V
-----------------------	-----------------
