



Pass and Seymour

Industrial Extra Heavy-Duty Specification Grade Switch, Light Almond
Part No. PS15AC2LA

2pole Toggle Switch, Back & Side Wire, 15amp 120/277volt, Ivory



Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- High strength thermoplastic polycarbonate toggle.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

UPC Number	785007195088	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Residential/Commercial
Standard	UL 20		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	120 V
Actuator	Toggle	Contact Rating	15amp, 120/277vac
Action	dpdt		