



**Legrand**  
Industrial Extra Heavy-Duty Specification Grade Switch, White  
Part No. PS20AC1WSL

1pole Lighted Switch, Back & Side Wire, 20amp 120/277volt, Ivory



## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Color White

UPC Number 785007260403

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Standard UL 20

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

---

<b>Wattage</b>	1 W
----------------	-----

---

<b>Number of Poles</b>	Single Pole
------------------------	-------------

---

<b>Voltage</b>	120 V
----------------	-------

---

<b>Closed Contact Resistance</b>	Toggle
----------------------------------	--------

---

<b>Contact Rating</b>	20amp, 120/277vac
-----------------------	-------------------

---