



2pole Pilot Lighted Switch, Back & Side Wire, 20amp 120/277volt, Clear

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Clear	UPC Number	785007195859
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL 20

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

Technical Information

Wattage	2 W	Number of Poles	Double Pole
Voltage	120 V	Closed Contact Resistance	Toggle
Contact Rating	20amp, 120/277vac		
