



Double Pole, Single Phase Switch, Back and Side Wire, HP Rated. 20 amps, 277 volts.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | |
|--------------------|----------------|
| Color | Brown |
| UPC Number | 785007195965 |
| Country Of Origin | Mexico |
| Product Line | Pass & Seymour |
| Application Sector | Industrial |
| Standard | UL 20 |

Listing Agencies / 3rd Party Agencies

| | |
|---------------------|--------|
| cULus Listed | Yes |
| cULus ListingNumber | 140597 |

Technical Information

| | |
|---------------------------|-------------|
| Wattage | 2 W |
| Number of Poles | Double Pole |
| Voltage | 120 V |
| Closed Contact Resistance | Toggle |

Contact Rating

20amp, 120/277vac
