



## Legrand

Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Gray  
Part No. PS20AC2L

2pole Lock Switch, Back & Side Wire, 20amp 120/277volt, White (Key can be removed in both positions)



### Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Color Gray

UPC Number 785007195620

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Standard UL 20

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

#### Technical Information

Wattage 2 W

---

<b>Number of Poles</b>	Double Pole
------------------------	-------------

---

<b>Voltage</b>	120 V
----------------	-------

---

<b>Closed Contact Resistance</b>	Toggle
----------------------------------	--------

---

<b>Contact Rating</b>	20amp, 120/277vac
-----------------------	-------------------

---