



Pass and Seymour
Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Gray
Part No. PS20AC2L

2pole Lock Switch, Back & Side Wire, 20amp 120/277volt, White (Key can be removed in both positions)



Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Color	Gray	UPC Number	785007195620
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL 20

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

Technical Information

Wattage	2 W	Number of Poles	Double Pole
---------	-----	-----------------	-------------

Voltage	120 V	Closed Contact Resistance	Toggle
---------	-------	---------------------------	--------

Contact Rating	20amp, 120/277vac
----------------	-------------------
