



## Legrand

Industrial Extra Heavy-Duty Specification Grade Switch, Lighted When On,  
Back & Side Wire, Red  
Part No. PS20AC2RPL

2pole Pilot Lighted Switch, Back & Side Wire, 20amp 120/277volt, Red



### Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Color Red

UPC Number 785007195866

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Standard UL20

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

#### Technical Information

Number of Poles Double Pole

---

<b>Voltage</b>	120 V
<b>Actuator</b>	Toggle
<b>Contact Rating</b>	20Amp, 120/277V
<b>Action</b>	DP

---