



Pass and Seymour
Industrial Extra Heavy Duty Specification Grade Switch, Black
Part No. PS20AC3BK



3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Industrial |
| Standard | UL 20 | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.25 in | Product Depth US | 1.09 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 4.195 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|----------------|-------------------|---------------------------|--------|
| Contact Rating | 20amp, 120/277vac | Closed Contact Resistance | Toggle |
|----------------|-------------------|---------------------------|--------|

| | | | |
|----------|------|-----------------|-------|
| Amperage | 20 A | Number of Poles | 3-Way |
|----------|------|-----------------|-------|

| | | | |
|---------|-----|---------|---------|
| Wattage | 3 W | Voltage | 120.0 V |
|---------|-----|---------|---------|
