



Legrand
Industrial Extra Heavy-Duty Specification Grade Switch, Clear
Part No. PS20AC3CSL

3way Lighted Switch, Back & Side Wire, 20amp 120/277volt, Light Almond



Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- High strength thermoplastic polycarbonate toggle.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-grounded clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Clear
UPC Number	785007195767
Country Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Industrial
Standard	UL 20

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
cULus ListingNumber	140597

Technical Information

Wattage	3 W
---------	-----

Number of Poles	3-Way
------------------------	-------

Voltage	120 V
----------------	-------

Closed Contact Resistance	Toggle
----------------------------------	--------

Contact Rating	20amp, 120/277vac
-----------------------	-------------------
