



3way Key Lock Back & Side Wire 20amp 120/277volt

## Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

## Specifications

### General Info

UPC Number	785007195675	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Standard	UL 20		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

### Technical Information

Wattage	3 W	Number of Poles	3-Way
Voltage	120 V	Closed Contact Resistance	Toggle
Contact Rating	20amp, 120/277vac		