



Pass and Seymour
Industrial Extra Heavy Duty Specification Grade Switch, Light Almond
Part No. PS20AC3LA



3-Way Toggle Switch, Back and Side-Wire, 20A 120/277V

Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 20

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Contact Rating	120/277vac, 20amp	Closed Contact Resistance	Toggle
Amperage	20 A	Number of Poles	3-Way
Wattage	3 W	Voltage	120.0 V