



Pass and Seymour  
Extra Heavy Duty Spec. Grade and Security Switches  
Part No. PS20AC4KL



4-Way Key Lock Back and Side-Wire 20A 120/277V

## Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Industrial     | Standard          | UL 20  |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.25 in  | Product Depth US | 1.09 in |
| Product Height US | 4.195 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|            |     |              |     |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

### Technical Information

|                |                   |                           |        |
|----------------|-------------------|---------------------------|--------|
| Contact Rating | 120/277vac, 20amp | Closed Contact Resistance | Toggle |
| Amperage       | 20 A              | Number of Poles           | 4-Way  |

---

|         |     |         |         |
|---------|-----|---------|---------|
| Wattage | 4 W | Voltage | 120.0 V |
|---------|-----|---------|---------|

---