



**Pass and Seymour**  
Series 16 In-Line Connectors  
Part No. PS20FBBK

400A 600V, Cable Size #2 - 2/0, Female Cam-Type Plug, Green



### Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance

Exceptional seal for maintaining NEMA Type 3R and 4 integrity

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity

Heavy-duty hex set screws allow greater termination torque

Copper wire provides quality strain relief

Copper shim bundles wire strands to reduce "splaying."

### Specifications

#### General Info

Color	Black	UPC Number	785007308105
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial/Industrial	Standard	UL, cCSAus

#### Technical Information

Number of Poles	Single Pole	Voltage	600 V
Wire Size	#2 - 2/0	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4