



Pass and Seymour  
Series 16 In-Line Connectors  
Part No. PS20FBG



400A 600V, Cable Size #2 - 2/0, Female Cam-Type Plug, Green

## Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance	Exceptional seal for maintaining NEMA Type 3R and 4 integrity
Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product	Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
Heavy-duty hex set screws allow greater termination torque	Copper wire provides quality strain relief
Copper shim bundles wire strands to reduce "splaying."	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Green
UPC Number	785007308143	Country Of Origin	Mexico
Features	Chemical Resistant	Application Sector	Commercial, Industrial
Standard	UL, cCSAus	Warranty Type	1-Year
Type	Connector		

### Technical Information

Flanged	No	Terminal Accommodation	2/0
Amperage	400 A	Number of Poles	Single Pole

Indoor/Outdoor	Indoor	Voltage	600.0 V
Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4		