



400A 600V M PLUG ORANGE #2-2/0

Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity.

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity.

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product.

Heavy-duty hex set screws allow greater termination torque.

Specifications

General Info

Product Line	Pass & Seymour	Color	Green
UPC Number	785007308044	Country Of Origin	Mexico
Features	Chemical Resistant	Application Sector	Commercial, Industrial
Standard	UL, cCSAus	Warranty Type	1-Year
Type	Connector		

Technical Information

Flanged	No	Terminal Accommodation	2/0
Amperage	400 A	Number of Poles	Single Pole
Indoor/Outdoor	Indoor	Voltage	600.0 V

Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
--------------------------	---
