



1pole Toggle Switch, Back & Side Wire, 30amp 120/277volt, Ivory

Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Cam controls fast "make" and positive "break" to minimize arcing.
- High strength thermoplastic polycarbonate toggle.
- Locking support provides resistance to face and back body separation.
- Grounding terminal is standard.
- Strap nickel-plated steel with integral ground.
- For covering patents, see www.legrand.us/patents.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Heavy-duty bumper pads for quiet operation.
- Back body made of glass-reinforced nylon.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Shallow design for ease of installation.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | |
|--------------------|------------------------|
| Color | Ivory |
| UPC Number | 785007195538 |
| Country Of Origin | Mexico |
| Product Line | Pass & Seymour |
| Application Sector | Residential/Commercial |
| Standard | UL20 |

Listing Agencies / 3rd Party Agencies

| | |
|---------------------|--------|
| cULus Listed | Yes |
| cULus ListingNumber | 140597 |

Technical Information

| | |
|-----------------|-------------|
| Number of Poles | Single Pole |
|-----------------|-------------|

| | |
|-----------------------|-----------------|
| Voltage | 120 V |
| Actuator | Toggle |
| Contact Rating | 30Amp, 120/277V |
| Action | SP |
