



# Pass and Seymour

Industrial Extra Heavy-Duty Specification Grade Switch, White  
Part No. PS30AC1W

1pole Toggle Switch, Back & Side Wire, 30amp 120/277volt, Ivory



## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Color	White	UPC Number	785007704754
-------	-------	------------	--------------

Country Of Origin	Mexico	Product Line	Pass & Seymour
-------------------	--------	--------------	----------------

Application Sector	Industrial	Standard	UL 20
--------------------	------------	----------	-------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Wattage	1 W	Number of Poles	Single Pole
---------	-----	-----------------	-------------

Voltage	120 V	Closed Contact Resistance	Toggle
---------	-------	---------------------------	--------

Contact Rating	30amp, 120/277vac
----------------	-------------------