



Pass and Seymour  
Pin & Sleeve Watertight 100A 250V Receptacle  
Part No. PS3100R6W



Double-Pole, Tamper-Resistant wire, Pin and Sleeve Receptacle.  
100A, 250V.

## Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | United States  | Application Sector | Commercial |
| Standard          | UL Listed      |                    |            |

### Dimensions

|                   |        |                   |        |
|-------------------|--------|-------------------|--------|
| Product Width US  | 5.2 in | Product Height US | 6.6 in |
| Product Length US | 5.6 in |                   |        |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 151348 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                 |             |          |         |
|-----------------|-------------|----------|---------|
| Number of Wires | 3           | Amperage | 100 A   |
| Number of Poles | Double Pole | Voltage  | 250.0 V |