



Pass and Seymour  
**30A 2 Pole 3 Wire Fusible Mechanical Interlock**  
Part No. PS330FMIR6W



Double pole, Triple wire, Fusible Mechanical Interlock Receptacle.  
30 amp, 240 vac.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007101089	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

### Technical Information

Phase	3	Number of Wires	3
Number of Poles	Double Pole	Voltage	240 V