



Double pole, Triple wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 120 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

| | | | |
|--------------------|---------------|--------------|----------------|
| Color | Gray | UPC Number | 785007421125 |
| Country Of Origin | United States | Product Line | Pass & Seymour |
| Application Sector | Industrial | Standard | UL Listed |

Technical Information

| | | | |
|-----------------|-------------|-----------------|-------|
| Number of Poles | Double Pole | Voltage | 120 V |
| Phase | 3 | Number of Wires | 3 |