



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS360MIR7W



Double pole, Triple wire, Non-Fusible Mechanical Interlock Receptacle. 60 amp, 480 vac.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Color	Gray	UPC Number	785007149302
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

### Technical Information

Number of Poles	Double Pole	Voltage	480 V
Phase	3	Number of Wires	3