



Pass and Seymour

Extra Heavy-Duty Spec. Grade 347VAC Toggle Switch Back & Side Wire, Black
Part No. PS371510BK



Canadian 1pole Switch, Back & Side Wire, 15amp 347volt, White

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Cam controls fast "make" and positive "break" to minimize arcing.

High strength thermoplastic polycarbonate toggle.

Locking support provides resistance to face and back body separation.

Grounding terminal is standard.

Strap nickel-plated steel with integral ground.

For covering patents, see www.legrand.us/patents.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Heavy-duty bumper pads for quiet operation.

Back body made of glass-reinforced nylon.

Oversized silver alloy contacts for long life and better heat dissipation.

Shallow design for ease of installation.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color	Black	UPC Number	785007196047
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 20

Technical Information

Number of Poles	Double Pole	Voltage	347 V
Actuator	Toggle	Contact Rating	15amp, 347vac
Action	dpdt		