

Canadian 1-Pole Switch, Back and Side-Wire, 15A 347V



## Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Ivory      |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL 20          |                    |            |

### Technical Information

|                |               |                           |             |
|----------------|---------------|---------------------------|-------------|
| Contact Rating | 15amp, 347vac | Closed Contact Resistance | Toggle      |
| Amperage       | 15 A          | Number of Poles           | Single Pole |
| Wattage        | 1 W           | Voltage                   | 347.0 V     |