



Canadian 1pole Switch, Back & Side Wire, 20amp 347volt, White

### Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.	Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
Cam controls fast "make" and positive "break" to minimize arcing.	Heavy-duty bumper pads for quiet operation.
High strength thermoplastic polycarbonate toggle.	Back body made of glass-reinforced nylon.
Locking support provides resistance to face and back body separation.	Oversized silver alloy contacts for long life and better heat dissipation.
Grounding terminal is standard.	Shallow design for ease of installation.
Strap nickel-plated steel with integral ground.	Auto-ground clip assures positive ground.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007196214
Country Of Origin	Mexico	Switch Type	Toggle
Application Sector	Industrial	Standard	UL 20
Type	Switch		

#### Technical Information

Contact Rating	20amp, 347vac	Amperage	20 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Wattage	1 W	Voltage	347.0 V