



Canadian 3way Switch, Back & Side Wire, 20amp 347volt, Ivory

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.	Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
Cam controls fast "make" and positive "break" to minimize arcing.	Heavy-duty bumper pads for quiet operation.
High strength thermoplastic polycarbonate toggle.	Back body made of glass-reinforced nylon.
Locking support provides resistance to face and back body separation.	Oversized silver alloy contacts for long life and better heat dissipation.
Grounding terminal is standard.	Shallow design for ease of installation.
Strap nickel-plated steel with integral ground.	Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007196252
Country Of Origin	Mexico	Features	Chemical Resistant
Switch Type	Toggle	Number of Switches	1

Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 20	Warranty Type	1-Year Limited Warranty
Type	Switch		
Technical Information			
Load Rating	20 A @ 347 VAC	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
Throw Type	Double Throw	Amperage	20 A
Number of Poles	3-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	347 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		