

Canadian 3way Switch, Back & Side Wire, 20amp 347volt, Ivory



### Features & Benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- High strength thermoplastic polycarbonate toggle.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Color	Brown	UPC Number	785007196252
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 20

#### Technical Information

Number of Poles	Double Pole	Voltage	347 V
Actuator	Toggle	Contact Rating	20amp, 347vac
Action	dpdt		