



Pass and Seymour
Series 16 In-Line Connectors
Part No. PS40FBBK



400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow

Features & Benefits

- | | |
|--|---|
| Thermoplastic elastomer housing for outstanding impact and chemical resistance | Exceptional seal for maintaining NEMA Type 3R and 4 integrity |
| Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product | Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity |
| Heavy-duty hex set screws allow greater termination torque | Copper wire provides quality strain relief |
| Copper shim bundles wire strands to reduce "splaying." | |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-----------------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | UL, cCSAus | | |

Dimensions

| | |
|-------------------|--------|
| Product Length US | 6.8 in |
|-------------------|--------|

Technical Information

| | | | |
|-----------|-----------|-----------------|-------------|
| Amperage | 400 A | Number of Poles | Single Pole |
| Wire Size | 2/0 - 4/0 | Voltage | 600.0 V |

| | |
|--------------------------|--|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |
|--------------------------|--|
