



Pass and Seymour
Series 16 In-Line Connectors
Part No. PS40FBBL

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow



Features & Benefits

- Thermoplastic elastomer housing for outstanding impact and chemical resistance
- Exceptional seal for maintaining NEMA Type 3R and 4 integrity
- Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product
- Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
- Heavy-duty hex set screws allow greater termination torque
- Copper wire provides quality strain relief
- Copper shim bundles wire strands to reduce "splaying."

Specifications

General Info

Color	Blue	UPC Number	785007308181
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial/Industrial	Standard	UL, cCSAus

Technical Information

Number of Poles	Single Pole	Voltage	600 V
Wire Size	2/0 - 4/0	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4