



Pass and Seymour
Series 16 In-Line Connectors
Part No. PS40FBG

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow



Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance

Exceptional seal for maintaining NEMA Type 3R and 4 integrity

Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product

Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity

Heavy-duty hex set screws allow greater termination torque

Copper wire provides quality strain relief

Copper shim bundles wire strands to reduce "splaying."

Specifications

General Info

Color	Green	UPC Number	785007308198
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial/Industrial	Standard	UL, cCSAus

Technical Information

Number of Poles	Single Pole	Voltage	600 V
Wire Size	2/0 - 4/0	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4