



Pass and Seymour  
Series 16 In-Line Connectors, Orange  
Part No. PS40FBO

400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow



## Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance	Exceptional seal for maintaining NEMA Type 3R and 4 integrity
Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product	Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
Heavy-duty hex set screws allow greater termination torque	Copper wire provides quality strain relief
Copper shim bundles wire strands to reduce "splaying."	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007422597	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL, cCSAus

### Dimensions

Product Length US	6.8 in
-------------------	--------

### Technical Information

Amperage	400 A	Number of Poles	Single Pole
----------	-------	-----------------	-------------

---

Wire Size	2/0 - 4/0	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4
-----------	-----------	--------------------------	---

---