



Pass and Seymour
100A 3 Pole 4 Wire Fusible Mechanical Interlock
Part No. PS4100FMIR12W



Triple pole, Four wire, Fusible Mechanical Interlock Receptacle. 100 amp, 120/240 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007101256	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Phase	3	Number of Wires	4
Number of Poles	3-Way	Voltage	120 V