



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock Receptacle.
20A, 3, 240V.

Features & Benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420449	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed

Technical Information

Phase	3	Number of Wires	4
Number of Poles	3-Way	Voltage	250 V