



Pass and Seymour Non-Fusible Mechanical Interlock Part No. PS430MIR5W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 3, 600 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Color	Gray	UPC Number	785007420470
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

Technical Information

Number of Poles	3-Way	Voltage	600 V
Phase	3	Wire Size	2Awg
Number of Wires	4		