



Pass and Seymour  
Non-Fusible Mechanical Interlock  
Part No. PS430MIR9W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 30 amp, 3, 240 vac.

## Features & Benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

## Specifications

### General Info

Color	Gray	UPC Number	785007420494
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

### Technical Information

Number of Poles	3-Way	Voltage	250 V
Phase	3	Wire Size	2Awg
Number of Wires	4		