



Pass and Seymour  
**Pin & Sleeve Watertight 32A 380V/415V Plug**  
Part No. PS432P6W

Triple-Pole, 4-Wire, Pin and Sleeve Watertight Plug. 32A, 380/415V.



## Features & Benefits

Legrand Pin & Sleeve products provide installation ease, enduring performance in harsh conditions, and guaranteed IEC 309 compatibility.

Nylon construction for high impact and corrosion resistance.

Locking ring with an integral neoprene gasket provides watertight seal when plug and connector/receptacle are mated.

Combination-head screws for added convenience and quick installation.

Cover with integral neoprene gasket provides watertight seal.

Arrives ready to wire, with cord grip open and cable-ready. Terminal screws come backed out and ready to wire. Front and back body require no disassembly prior to assembly.

Nickel-plated brass pins provide extra corrosion resistance without sacrificing electrical conductivity.

Natural-rubber grommets provide watertight protection at cable entry.

Revolutionary, hinged cord grip for durable performance and ease of installation.

## Specifications

### General Info

|               |                |                    |               |
|---------------|----------------|--------------------|---------------|
| Product Line  | Pass & Seymour | Color              | Gray          |
| UPC Number    | 785007142914   | Country Of Origin  | United States |
| Features      | Watertight     | Application Sector | Industrial    |
| Warranty Type | 1-Year         | Type               | Plug          |

### Dimensions

|                  |        |                   |        |
|------------------|--------|-------------------|--------|
| Product Width US | 3.7 in | Product Height US | 3.7 in |
|------------------|--------|-------------------|--------|

|                   |        |
|-------------------|--------|
| Product Length US | 6.5 in |
|-------------------|--------|

Technical Information

|                 |              |          |           |
|-----------------|--------------|----------|-----------|
| Connector Style | Pin & Sleeve | Flanged  | No        |
| Number of Wires | 4            | Amperage | 32 A      |
| Indoor/Outdoor  | Both         | Voltage  | 380/415 V |