



Pass and Seymour
Non-Fusible Mechanical Interlock
Part No. PS460MIR5W



Triple-Pole, 4-Wire, Non-Fusible Mechanical Interlock Receptacle.
60A, 3, 600V.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007420579	Country Of Origin	United States
Application Sector	Commercial	Standard	UL Listed

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Phase	3	Number of Wires	4
Number of Poles	3-Way	Wire Size	2Awg
Voltage	600 V		