



Pass and Seymour
Non-Fusible Mechanical Interlock
Part No. PS460MIR7W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 60 amp, 3, 480 vac.

Features & Benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

Specifications

General Info

Color	Gray	UPC Number	785007420586
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL Listed

Technical Information

Number of Poles	3-Way	Voltage	480 V
Phase	3	Wire Size	2Awg
Number of Wires	4		