



Pass and Seymour
60A Pin and Sleeve Receptacle
Part No. PS460R5W

Triple-Pole, 4-Wire, Pin and Sleeve Receptacle. 60A, 3/600V.



Features & Benefits

All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.

And all feature chemical-resistant thermoplastic construction.

An exclusive, hinged cord grip eliminates loose parts that get lost.

North American products come completely ready to wire, for quick, simple installation.

Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | UL Listed | | |

Dimensions

| | | | |
|-------------------|--------|-------------------|--------|
| Product Width US | 4.2 in | Product Height US | 6.6 in |
| Product Length US | 5.0 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 151348 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------|---------|-----------|-------|
| Number of Wires | 4 | Amperage | 60 A |
| Number of Poles | 3-Way | Wire Size | 2 AWG |
| Voltage | 600.0 V | | |
